
FABORY



# DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M5X25

| | |
|---|---|
| Article number | 08250.050.025 |
| Brand | - |
| UBB | 950351599796 |
| UNSPSC | 31161612 |
| EAN | 8715492554734 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M5 |
| Length | 25 mm |
| Class | 4.6 |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | The property class of the corresponding nuts is \|4\| as a minimum.Depending the supplier material class can differ (4.6 or 4.8) |


## Standards

| | |
|---|---|
| NEN | ≈303/697 |
| BS | ≈4933/3692 |
| ISO | ≈8677/4034 |
| DIN | 603/555 |
| NF | ≈E27-351/E25-402 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 22 |
| b (min.): L≤125mm | 16 |
| d-D | M5 |
| dk (max.) | 13.55 |
| k (max.) | 3.3 |
| L (mm) | 25 |
| m | 4 |
| P | 0.8 |
| fn (max.) | 4.1 |

## Technical Drawing



| | |
|---|---|
| s | 8 |
| Vn (max.) | 5.48 |