
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M5X70

Article number	08250.050.070
Brand	-
UBB	950351600503
UNSPSC	31161612
EAN	8715492554819
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	70 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

BS	≈4933/3692
ISO	≈8677/4034
NEN	≈303/697
NF	≈E27-351/E25-402
DIN	603/555

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
dk (max.)	13.55
k (max.)	3.3
L (mm)	70
m	4
P	0.8
fn (max.)	4.1

Technical Drawing



s	8
Vn (max.)	5.48