
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M6X130

Article number	08250.060.130
Brand	-
UBB	500621753986
UNSPSC	31161612
EAN	8715494507660
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	130 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

NEN	≈303/697
BS	≈4933/3692
ISO	≈8677/4034
DIN	603/555
NF	≈E27-351/E25-402

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
dk (max.)	16.55
k (max.)	3.88
L (mm)	130
m	5
P	1
fn (max.)	4.6

Technical Drawing



s	10
Vn (max.)	6.48