
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M10X30

Article number	08250.100.030
Brand	-
UBB	950351605064
UNSPSC	31161612
EAN	8715492555458
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	30 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

NF	≈E27-351/E25-402
DIN	603/555
NEN	≈303/697
BS	≈4933/3692
ISO	≈8677/4034

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
dk (max.)	24.65
k (max.)	5.38
L (mm)	30
m	8
P	1.5

Technical Drawing



fn (max.)	6.6
s	17
Vn (max.)	10.58