
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M10X50

Article number	08250.100.050
Brand	-
UBB	950351605486
UNSPSC	31161612
EAN	8715492555496
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

BS	≈4933/3692
DIN	603/555
NEN	≈303/697
NF	≈E27-351/E25-402
ISO	≈8677/4034

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
dk (max.)	24.65
k (max.)	5.38
L (mm)	50
m	8
P	1.5

Technical Drawing



fn (max.)	6.6
s	17
Vn (max.)	10.58