
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M10X260

Article number	08250.100.260
Brand	-
UBB	950351607532
UNSPSC	31161612
EAN	8715492555717
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	260 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

DIN	603/555
ISO	≈8677/4034
NF	≈E27-351/E25-402
BS	≈4933/3692
NEN	≈303/697

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
dk (max.)	24.65
k (max.)	5.38
L (mm)	260
m	8
P	1.5

Technical Drawing



fn (max.)	6.6
s	17
Vn (max.)	10.58