
FABORY



DIN 603/555 Coach Bolt with Hexagon Nut, Zinc Plated, 4.6 M12X75

Article number	08250.120.075
Brand	-
UBB	950351609025
UNSPSC	31161612
EAN	8715492555908
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	75 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The property class of the corresponding nuts is |4| as a minimum.Depending the supplier material class can differ (4.6 or 4.8)


Standards

BS	≈4933/3692
NF	≈E27-351/E25-402
NEN	≈303/697
ISO	≈8677/4034
DIN	603/555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
dk (max.)	30.65
k (max.)	6.95
L (mm)	75
m	10
P	1.75

Technical Drawing



fn (max.)	8.75
s	19
Vn (max.)	12.7