
FABORY



Knurled thumb screw high type DIN 464 Free-cutting steel Plain M10X40

Article number	16649.100.040
Brand	-
UBB	500647868040
UNSPSC	31161500
EAN	8717077276567
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Material	Free-cutting steel
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	464

Technical Specification

b	30
d-D	M10
dk	36
ds	20
Full thread if L ≤	30
h	23
k	8
L (mm)	40
P	1.5

Technical Drawing

