FABORY



Knurled thumb screw thin type DIN 653 Steel Plain M4X25

Article number	16659.040.025
Brand	-
UBB	500649315586
UNSPSC	31161500
EAN	8717077262188
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	653

Technical Specification

d-D	M4
dk	16
e	3
Full thread if L ≤	16
k	3.5
L (mm)	25
P	0.7

Technical Drawing

