
FABORY



Double end stud with reduced shank with 2 hexagon nuts DIN 2510 L/NF Steel 21CrMoV5-7+QT (1.7709)/25CrMo4+QT (1.7218) Plain M16X150

Article number	23530.160.150
Brand	-
UBB	500644895657
UNSPSC	31161619
EAN	8717077038967
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	150 mm
Marking	GA/KG
Material	Steel
Material technical	21CrMoV5-7+QT (1.7709)/25CrMo4+QT (1.7218)
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	External thread with large clearance according to DIN 2510-2.


Standards

DIN	2510-L/NF

Technical Specification

b	23
d-D	M16
d2	12
L (mm)	150
m	16
P	2

Technical Drawing



FABORY