FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X50

Article number	24520.060.050
Brand	-
UBB	950353119924
UNSPSC	31161504
EAN	8715492630971
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-127
ISO	≈1207
BS	≈4183
DIN	84
ASME	≈B18.6.7M
NEN	≈1602

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	50
n	1.6
P	1
t (min.)	1.6

Technical Drawing