FABORY



# Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M8X80

| | |
|---|---|
| Article number | 24520.080.080 |
| Brand | - |
| UBB | 950353121722 |
| UNSPSC | 31161504 |
| EAN | 8715492631282 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M8 |
| Length | 80 mm |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Cylindrical head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ISO | ≈1207 |
| ASME | ≈B18.6.7M |
| NEN | ≈1602 |
| DIN | 84 |
| NF | ≈E25-127 |
| BS | ≈4183 |

## Technical Specification

| | |
|---|---|
| d-D | M8 |
| Thread length (min.) | 38 |
| dk (max.) | 13 |
| Full thread if L ≤ | 40 |
| k (max.) | 5 |
| L (mm) | 80 |
| n | 2 |
| P | 1.25 |
| t (min.) | 2 |

## Technical Drawing