FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2,5X10

Article number	24540.025.010
Brand	-
UBB	950353130145
UNSPSC	31161504
EAN	8715492632630
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
ASME	≈B18.6.7M
BS	≈4183
DIN	963
ISO	≈2009
NF	≈E25-123

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	10
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

