FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X70

Article number	24540.030.070
Brand	-
UBB	500621767507
UNSPSC	31161504
EAN	8715494509084
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	70
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

