FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X100

Article number	24540.030.100
Brand	-
UBB	950353132539
UNSPSC	31161504
EAN	8715492633033
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
NEN	≈2370
ISO	≈2009
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	100
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

