FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X6

Article number	24540.050.006
Brand	-
UBB	950353135193
UNSPSC	31161504
EAN	8715492633361
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2009
DIN	963
NF	≈E25-123

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	6
n	1.2
P	0.8
t (min.)	1

Technical Drawing

