FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X80

Article number	24540.050.080
Brand	-
UBB	950353136597
UNSPSC	31161504
EAN	8715492633552
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
ISO	≈2009
NEN	≈2370
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	80
n	1.2
P	0.8
t (min.)	1

Technical Drawing

