FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M12X35

Article number	24540.120.035
Brand	-
UBB	950353141035
UNSPSC	31161504
EAN	8715492634184
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
DIN	963
NEN	≈2370

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if L ≤	60
k (max.)	6
L (mm)	35
n	3
P	1.75
t (min.)	2.4

Technical Drawing

