FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M16X45

Article number	24540.160.045
Brand	-
UBB	950353142025
UNSPSC	31161504
EAN	8715492634337
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	45 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M
BS	≈4183
DIN	963
NEN	≈2370

Technical Specification

d-D	M16
Thread length (min.)	58
dk (max.)	29
Full thread if L ≤	70
k (max.)	8
L (mm)	45
n	5
P	2
t (min.)	3.2

Technical Drawing

