FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X40

Article number	24540.200.040
Brand	-
UBB	950353142777
UNSPSC	31161504
EAN	8715492634405
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M20
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M
ISO	≈2009
DIN	963

Technical Specification

d-D	M20
Thread length (min.)	70
dk (max.)	36
Full thread if L ≤	80
k (max.)	10
L (mm)	40
n	5
P	2.5
t (min.)	4

Technical Drawing

