FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X50

Article number	24540.200.050
Brand	-
UBB	950353142850
UNSPSC	31161504
EAN	8715492634412
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M20
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123
DIN	963
NEN	≈2370

Technical Specification

d-D	M20
Thread length (min.)	70
dk (max.)	36
Full thread if L ≤	80
k (max.)	10
L (mm)	50
n	5
P	2.5
t (min.)	4

Technical Drawing

