FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M3X8

Article number	24565.030.008
Brand	-
UBB	951353774148
UNSPSC	31161504
EAN	8715492635266
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
NF	≈E25-123
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	8
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

