FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X20

Article number	24570.030.020
Brand	-
UBB	950353147800
UNSPSC	31161504
EAN	8715492635914
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2010
NF	≈E25-124
BS	≈4183
NEN	≈2371
DIN	964

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	20
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

