FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X6

Article number	24570.040.006
Brand	-
UBB	950353148220
UNSPSC	31161504
EAN	8715492635983
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-124
ISO	≈2010
NEN	≈2371
DIN	964
BS	≈4183

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	6
n	1
P	0.7
t (min.)	1.6

Technical Drawing

