
FABORY



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X8

Article number	24640.050.008
Brand	-
UBB	950353154236
UNSPSC	31161504
EAN	8715492637475
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

NEN	≈1603
NF	≈E25-128
ASME	≈B18.6.7M
DIN	85
ISO	≈1580
BS	≈4183

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3
L (mm)	8
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

