
FABORY



Double slotted mushroom head screw NF E25-129 Steel Zinc plated 4.8 M8X100

Article number	24862.080.100
Brand	-
UBB	951353018447
UNSPSC	31162400
EAN	8715493594081
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Button head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-129

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	20
Full thread if L ≤	60
k (max.)	4.4
L (mm)	100
n	2
P	1.25
t (min.)	2

Technical Drawing

