FABORY



Bearing preload disc spring Spring steel Phosphated 31,7X20,4X0,4MM

Article number	36460.337.004
Brand	-
UBB	950357490685
UNSPSC	31161811
EAN	8715492763051
PKG. of 25	Full Box Only

Technical Parameters


Diameter	20.4 mm
d_e	31.7
di	20.4
Material	Spring steel
Outer diameter	31.7
Surface treatment	Phosphated
Info	Warning: electroplating of these products may cause hydrogen embrittlement.F = spring load in Newton at a deflection s ≈ 0,75 h0 (h0 = l0 - t).Extensive technical data available on request.

Standards

Technical Specification

di (H12)	20.4
D (mm)	20.4
F	81
l0	1.1
t	1.09

Technical Drawing



Thickness 0.4

FABORY