FABORY



Bearing preload disc spring Spring steel Phosphated 54,5X40,5X0,6MM

Article number	36460.585.006
Brand	-
UBB	950357491006
UNSPSC	31161811
EAN	8715492763129
PKG. of 10	Full Box Only

Technical Parameters


Diameter	40.5 mm
d_e	54.5
di	40.5
Material	Spring steel
Outer diameter	54.5
Surface treatment	Phosphated
Info	Warning: electroplating of these products may cause hydrogen embrittlement.F = spring load in Newton at a deflection s ≈ 0,75 h0 (h0 = l0 - t).Extensive technical data available on request.

Standards

Technical Specification

di (H12)	40.5
D (mm)	40.5
F	141
l0	1.5
t	1.5

Technical Drawing



Thickness 0.6

FABORY