FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M5X40

Article number	51230.050.040
Brand	-
UBB	500571474930
UNSPSC	31161518
EAN	8715494114028
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NEN	2344
NF	E27-182
ISO	4028
DIN	915
BS	4168-4
ASME	B18.3.6M

Technical Specification

d-D	M5
dp (max.)	3.5
L (mm)	40
P	0.8
s	2.5
t (min.)	2
z long (min.)	2.5
z long if L ≥	8
z short (min.)	1.25

Technical Drawing

