FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M6X60

Article number	51230.060.060
Brand	-
UBB	500571475432
UNSPSC	31161518
EAN	8715494114073
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NEN	2344
ISO	4028
NF	E27-182
BS	4168-4
ASME	B18.3.6M
DIN	915

Technical Specification

d-D	M6
dp (max.)	4
L (mm)	60
P	1
s	3
t (min.)	2
z long (min.)	3
z long if L ≥	10
z short (min.)	1.5

Technical Drawing

