FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M12X35

Article number	51230.120.035
Brand	-
UBB	500571476919
UNSPSC	31161518
EAN	8715494114226
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	35 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NEN	2344
NF	E27-182
DIN	915
ASME	B18.3.6M
BS	4168-4
ISO	4028

Technical Specification

d-D	M12
dp (max.)	8.5
L (mm)	35
P	1.75
s	6
t (min.)	4.8
z long (min.)	6
z long if L ≥	20
z short (min.)	3

Technical Drawing

