FABORY



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M12X50

Article number	51230.120.050
Brand	-
UBB	500571477255
UNSPSC	31161518
EAN	8715494114257
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ASME	B18.3.6M
ISO	4028
NF	E27-182
NEN	2344
BS	4168-4
DIN	915

Technical Specification

d-D	M12
dp (max.)	8.5
L (mm)	50
P	1.75
s	6
t (min.)	4.8
z long (min.)	6
z long if L ≥	20
z short (min.)	3

Technical Drawing

