FABORY



Slotted set screw with cone point DIN 553 Stainless steel A1/A2 M5X25

Article number	51293.050.025
Brand	-
UBB	951351826247
UNSPSC	31161505
EAN	8715492280848
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Driving features	Slotted
Material	Stainless steel
Material technical	A1/A2
Thread direction	Right
Point	Cone
Thread	Metric thread
Info	Depending on availability A1 can be supplied as well as A2.

Standards

NEN	1488
ISO	7434
DIN	553
BS	4219
NF	E25-161

Technical Specification

d-D	M5
dt (max.)	0.5
L (mm)	25
n	0.8
P	0.8

Technical Drawing

