FABORY



Slotted set screw with cone point DIN 553 Stainless steel A1/A2 M10X25

Article number	51293.100.025
Brand	-
UBB	500571486405
UNSPSC	31161505
EAN	8715494100540
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	25 mm
Driving features	Slotted
Material	Stainless steel
Material technical	A1/A2
Thread direction	Right
Point	Cone
Thread	Metric thread
Info	Depending on availability A1 can be supplied as well as A2.

Standards

ISO	7434
BS	4219
NF	E25-161
NEN	1488
DIN	553

Technical Specification

d-D	M10
dt (max.)	2.5
L (mm)	25
n	1.6
P	1.5

Technical Drawing

