FABORY



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M3X4

Article number	51302.030.004
Brand	-
UBB	951353118841
UNSPSC	31161504
EAN	8715492282095
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	4
No. cross recess	1
P	0.5

Technical Drawing

