
FABORY



Hexalobular countersunk head screw DIN ≈965 A Stainless steel A2 M2,5X3

Article number	51305.025.003
Brand	-
UBB	500512301549
UNSPSC	31161504
EAN	8715494275408
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	3 mm
Class	70
Driving features	Hexalobular
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	≈965
NF	≈E25-119-1
ISO	≈14581

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	3
P	0.45
Socket	8

Technical Drawing

