FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M8X140

Article number	53510.080.140
Brand	-
UBB	500571355717
UNSPSC	31161620
EAN	8715494111805
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	140 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	140
P	1.25
s	13

Technical Drawing

