FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M10X55

Article number	53510.100.055
Brand	-
UBB	500571356053
UNSPSC	31161620
EAN	8715494111836
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	55 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NF	E25-112
NEN	1555
ISO	4014
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	55
P	1.5

Technical Drawing

