FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Stainless Steel A4-80 M20X65

Article number	53510.200.065
Brand	-
UBB	500571358034
UNSPSC	31161620
EAN	8715494143646
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	65 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	65
P	2.5

Technical Drawing

