FABORY



KIPP Clamping levers with locating hole, non-adjustable Black Steel 5.8/plastic Zinc plated 8MM

Article number	58083.000.008
Brand	-
UBB	500689668241
UNSPSC	31162807
EAN	4059245071494
PKG. of 15	Full Box Only

Technical Parameters

Class	5.8
Color	Black
D1_MM	18.3mm
Material	Steel/plastic
Surface treatment	Zinc plated
Info	Material: Handle fibreglass reinforced plastic. Steel parts grade 5.8.Version: Handle in anthracite grey, steel parts zinc plated, blue passivated.Note: Non-adjustable clamping levers can be used for simple applications. Generally there must be enough space so that the lever can be turned 360°.

Standards

Technical Specification

A	65
A1	75
B	9
D1	18.3

Technical Drawing

D2	18.5
H	18
H2	36.5
H1	11
T1	14
X	8

FABORY

