FABORY



KIPP Cam levers, external thread Stainless steel 1.4308/1.4305 M5X40

Article number	58119.050.040
Brand	-
UBB	500689942307
UNSPSC	31162807
EAN	4059245209392
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	18.1mm
Material	Stainless steel
Material technical	1.4308/1.4305
Thread	Metric thread
Info	Material: Handles 1.4308. Thrust washer plastic PA 66 GF 35-X fibreglass reinforced. Hinge pin, washer and screw 1.4305.Version: Handle electropolished. Thrust washer black. Hinge pin, washer and screw bright.Note: Adjustable cam levers are used if the position of the lever relative to the axis of tension only permits one specific position (interference circle). The exact position of the lever is adjusted using a screwdriver on the fine thread setscrew. Plastics are subject to

Standards

	creeping under load (retardation).Drawing reference: 1) setscrew for fine adjustment of lever.adjustable

Technical Specification

A	70.4
A1	79.2
B	21.5
B1	15
Hand force FH (N)	120
D	5
D1	18.1
D2	9
F	4
H	14.5
H1	22
L	40
S	1.2

Technical Drawing

