FABORY



FAC RATCHET VR.J154 3/8

Article number	6D928877
Brand	-
UBB	500637297226
UNSPSC	27111753
EAN	3148519221954
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.2
Tool insertion	3/8 inch
Idle rotational speed	300
Air inlet device-sided	R 1/4 inch
Max. loosening torque	54
Ratcheting model	Yes
Air volume required	110

Standards