
FABORY



Steel Zinc plated yellow passivated M8X115

Article number	70410.080.115
Brand	-
UBB	950352652636
UNSPSC	31161607
EAN	8715492904225
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	115 mm
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Type no.	M

Standards

Technical Specification

Concrete C20/25	1.6
Concrete C28/35	2
d-D	M8
Drill depth (min.)	55
Drill ø	8
Grip range (max.)	60
L (mm)	115

Technical Drawing

