FABORY



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc plated yellow passivated Gr.B7 - Gr.2H 3/4X70 (2.3/4)

Article number	PIMI2191070
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	70 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated yellow passivated
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194

Technical Specification

L (mm)	70

Technical Drawing

FABORY

