FABORY



Studbolt with 2 heavy hexagon nuts ASTM A193/A194 Steel Hot dip galvanized Gr.B7 - Gr.2H 5/8X85 (3.3/8)

Article number	PIMI4158085
Brand	-
UBB	500636933656
UNSPSC	00000000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	85 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Hot dip galvanized
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194

Technical Specification

L (mm)	85

Technical Drawing

FABORY

