FABORY



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Stainless steel Plain Gr.B8M Cl.2 - Gr.8M 7/8X210 (8.1/4)

Article number	PIMPF222210
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	210 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Surface treatment	Plain
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194

Technical Specification

L (mm)	210

Technical Drawing

FABORY

