FABORY



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Stainless steel Plain Gr.B8M - Gr.8MA 1.1/8X260 (10.1/4)

Article number	PIMPG285260
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/8 Inch
Length	260 mm
Class	Gr.B8M - Gr.8MA
Material	Stainless steel
Surface treatment	Plain
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194

Technical Specification

L (mm)	260

Technical Drawing

FABORY

