FABORY



Studbolt with 2 heavy hexagon nuts ASME SA193/ SA194 Steel Plain Gr.B7 - Gr.2H 1.1/8X360 (14.1/4)

Article number	PIMT0285360
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/8 Inch
Length	360 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Plain
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	SA193/SA194

Technical Specification

L (mm)	360

Technical Drawing

FABORY

