FABORY



M20X290

Numéro d'article	90293FIS
Marque	-
UBB	500616697149
UNSPSC	31161601
EAN	4006209902936
PKG. de 10	Boîte complete uniquement

Paramètres techniques

Diamètre	M20
Longueur	290 mm
ETA-approval	Yes
Info	Ccr, N = Characteristic Edge distance (tensile).Cmin. = Minimum edge distance (tensile).df = Hole diameter in fixture.do = Hole diameter in substrate.hef = Effective embedment depth.hmin = Minimum substrate thickness.ho = Minimum hole depth.Scr, N = Characteristic spacing.Concrete C20/25 recommended load for non-cracked concrete.The allowable load is only valid for AcryMaxx Chemical Mortar in combination with Anchor studs, steel grade 5.8.The allowable load is valid for one single

Normes

anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor γf= 1,4 and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Spécifications techniques

Dessin technique

