FABORY



M10X120 K

Cikkszám	0Z685162
Márka	-
UBB	500636513979
UNSPSC	31161601
EAN	4042205233445
csom. 1	Csak bontatlan csomagban

Műszaki **adatok**

Készlet tartalma	4 x FIS G M 10 x 120, washer + nut
Info	Ccr, N = Characteristic Edge distance (tensile).Cmin. = Minimum edge distance (tensile).df = Hole diameter in fixture.do = Hole diameter in substrate.hef = Effective embedment depth.hmin = Minimum substrate thickness.ho = Minimum hole depth.Scr, N = Characteristic spacing.Concrete C20/25 recommended load for non-cracked concrete.The allowable load is only valid for AcryMaxx Chemical Mortar in combination with Anchor studs, steel grade 5.8.The allowable load is valid for one single anchor, at cracked concrete (tensile

Szabványok

zone) with concrete class C20/25, incl. partial safety factor γf= 1,4 and if the Scr, N and Ccr, N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Műszaki **specifikációk**

Műszaki **rajz**

